



## QT607

Quantec slave ceiling pull unit



## Overview

Can be used to generate a Standard or Ensuite call on aQuantec Addressable Call System.

Typically wired as a slave to aQuantec Addressable Call Point or Quantec Accessible Toilet Reset Point.

Supplied with 3m of red nylon pull cord and two red open-sided triangular bangles for ease of use by the infirm.

Red confidence LED and diffuser emits a bright red glow over a wide area to reassure the user that a call has been made.

Surface mountable.

Base fits 16mm conduit and BESA centres.

Also available as part of the QT951 Accessible Toilet Expansion Kit.

# Technical Specifications

Quiescent current	Less than 3mA.
Alarm current	6mA.
Indicators	Red reassurance LED/diffuser (active in Alarm).
Controls	Red pull cord (activated by pulling one of the QT607's bangles).
Connections	Local +V; S (Switch); R (Red). Wire as a slave to a Quantec Addressable Call Point or Accessible Toilet Reset Point. See instructions for details.
Onboard Sounder	No.
Product dimensions (mm)	93mm diameter x 27mm deep. Designed for ceiling mounting only. Base fits 16mm conduit and BESA centres.
Construction & finish	Plastic.
IP Rating	IP21.
Weight	56g.
Operating conditions/temperature	-5°C to +40°C. Max. relative humidity 95% non-condensing.

Datasheet generated from <https://www.electrika.com> last updated Wednesday, January 16, 2019 11:46:02 AM